
FABORY



Prevailing torque type hexagon nut with non-metallic insert, high type DIN 982 Steel Zinc plated 8 M5

Article number	12600.050.001
Brand	-
UBB	950355134988
UNSPSC	31161727
EAN	8715492579461
PKG. of 250	Full Box Only

Technical Parameters

Diameter	M5
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈7040
DIN	982
NF	≈E25-409

Technical Specification

d-D	M5
h	6.3
P	0.8
s	8

Technical Drawing

