
FABORY



Prevailing torque type hexagon nut with non-metallic insert, high type DIN 982 Steel Zinc plated 8 M6

Article number	12600.060.001
Brand	-
UBB	950355135068
UNSPSC	31161727
EAN	8715492579478
PKG. of 250	Full Box Only

Technical Parameters

Diameter	M6
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	982
NF	≈E25-409
ISO	≈7040

Technical Specification

d-D	M6
h	8
P	1
s	10

Technical Drawing

