
FABORY



Prevailing torque type hexagon nut, all metal DIN 980V Steel Zinc plated 8 M8

Article number	12858.080.001
Brand	-
UBB	950355778651
UNSPSC	31161727
EAN	8715492579973
PKG. of 250	Full Box Only

Technical Parameters

Diameter	M8
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	2452
ISO	7042
DIN	980-V
NF	E25-410
BS	4929-1

Technical Specification

d-D	M8
h (max.)	8
P	1.25
s	13

Technical Drawing

