
FABORY



Prevailing torque type hexagon nut, all metal DIN 980V Steel Zinc plated 8 M12

Article number	12858.120.001
Brand	-
UBB	950355778818
UNSPSC	31161727
EAN	8715492579997
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	7042
BS	4929-1
DIN	980-V
NEN	2452
NF	E25-410

Technical Specification

d-D	M12
h (max.)	12
P	1.75
s	19

Technical Drawing

