
FABORY



Prevailing torque type hexagon nut, all metal DIN 980V Steel Zinc plated 8 M16

Article number	12858.160.001
Brand	-
UBB	950355778990
UNSPSC	31161727
EAN	8715492580016
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M16
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	980-V
BS	4929-1
ISO	7042
NF	E25-410
NEN	2452

Technical Specification

d-D	M16
h (max.)	16
P	2
s	24

Technical Drawing

