
FABORY



Prevailing torque type hexagon nut, all metal DIN 980V Steel Zinc plated 8 M36

Article number	12858.360.001
Brand	-
UBB	500621924272
UNSPSC	31161727
EAN	8715494515559
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M36
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	7042
DIN	980-V
NF	E25-410
BS	4929-1
NEN	2452

Technical Specification

d-D	M36
h (max.)	36
P	4
s	55

Technical Drawing

