
FABORY



Hexagon weld nut DIN 929 Steel Max. 0,25%C Plain M8

Article number	14020.080.001
Brand	-
UBB	950355149184
UNSPSC	31161731
EAN	8715492581747
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M8
Driving features	Hexagon
Material	Steel
Material technical	Max. 0.25%C
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	These weld nuts are intended for use with fasteners in property classes 8.8

Standards

DIN	929

Technical Specification

d-D	M8
Hole ø (H11)	10.5
m (h14)	6.5
P	1.25
s (h13)	14

Technical Drawing

