
FABORY



Hex press nut Kh=1,8 Steel Zinc plated 6 Kh=1,8 M5

Article number	15020.050.001
Brand	-
UBB	950355645413
UNSPSC	31161724
EAN	8715492583321
PKG. of 250	Full Box Only

Technical Parameters

Diameter	M5
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Kh=1,8

Standards

Technical Specification

d-D	M5
d2	6.75
h	5
Hole ø (H11)	6.5
kh	1.8
m	3.2
Material thickness (min.)	2
P	0.8
s	8

Technical Drawing

