FABORY



Eye bolt DIN 444 B Steel Zinc plated 4.6 M10X75

Article number	16181.100.075
Brand	-
UBB	500647859130
UNSPSC	31161610
EAN	8717077275669
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M10
Length	75 mm
Class	4.6
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	444-B

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L≤125mm	26
d-D	M10
d2(H9)	10
d3 (max.)	20
L (mm)	75
P	1.5
s (max.)	12

Technical Drawing

