FABORY



Eye bolt fully threaded DIN 444 LB Steel Zinc plated 4.6 M24X150

Article number	16182.240.150
Brand	-
UBB	500644873043
UNSPSC	31161610
EAN	8717077035904
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M24
Length	150 mm
Class	4.6
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	444-LB

Technical Specification

d-D	M24
d2(H9)	22
d3 (max.)	45
L (mm)	150
Lg (max.)	40
P	3
s (max.)	25

Technical Drawing

