
FABORY



T-head bolt with square neck DIN 186 B Steel Plain 4.6 M24X120

Article number	16190.240.120
Brand	-
UBB	950351692591
UNSPSC	31161617
EAN	8715492587534
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M24
Length	120 mm
Class	4.6
Material	Steel
Surface treatment	Plain
Thread	Metric thread
Info	For sizes of T-slots, see DIN 649.

Standards

DIN	186-B

Technical Specification

d-D	M24
k	15
L (mm)	120
Lg (max.)	37
m	43
n	24
P	3

Technical Drawing

