
FABORY



U-Bolt type B Steel Zinc plated M8X61X44X30

Article number	17243.080.044
Brand	-
UBB	408373264758
UNSPSC	31161616
EAN	8712547003940
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M8
Length	61 mm
D (Inch)	1inch
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

Technical Specification

b	30
d-D	M8
d	8
D (mm)	34
E	44
For pipe ø	1
L (mm)	61
L1	53
L2	36
L3	19

Technical Drawing

