FABORY



Slotted set screw with cone point DIN 553 Steel Plain 14H M10X25

Article number	20030.100.025
Brand	-
UBB	500645185538
UNSPSC	31161505
EAN	8717077069183
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	25 mm
Class	14H
Driving features	Slotted
Material	Steel
Thread direction	Right
Point	Cone
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	553
BS	4219
ISO	7434
NEN	1488
NF	E25-161

Technical Specification

d-D	M10
dt (max.)	2.5
L (mm)	25
n	1.6
P	1.5

Technical Drawing

