FABORY



Threaded rod DIN 976-1A Plain Steel 12.9 1 mtr M27

Article number	20132.270.001
Brand	-
UBB	951353652112
UNSPSC	31161618
EAN	8715492604576
PKG. of 2	Full Box Only

Technical Parameters

Diameter	M27
Length	1000 mm
Class	12.9
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.1 meter

Standards

DIN	976-1A
NF	E25-136

Technical Specification

d-D	M27
L (mm)	1000
P	3

Technical Drawing

