FABORY



Threaded rod length 1 metre DIN 976-1A Steel Zinc plated 8.8 M8

Article number	20230.080.001
Brand	-
UBB	950353012582
UNSPSC	31161618
EAN	8715492605818
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M8
Length	1000 mm
Class	8.8
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	1 meter

Standards

DIN	976-1A
NF	E25-136

Technical Specification

d-D	M8
L (mm)	1000
P	1.25

Technical Drawing

