FABORY



Threaded rod DIN 976-1A Zinc Plated (BZP) 4.8 M12X1,25

Article number	20360.120.125
Brand	-
UBB	950353027101
UNSPSC	31161618
EAN	8715492607690
PKG. of 2	Full Box Only

Technical Parameters

Diameter	M12
Length	1000 mm
Class	4.8
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric fine thread

Standards

NF	≈E25-136
DIN	976-1

Technical Specification

d-D	M12
L (mm)	1000
P	1.25

Technical Drawing

