FABORY



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7M - Gr.2HM 1.3/8X300 (11.3/4)

Article number	22086.349.298
Brand	-
UBB	500578813809
UNSPSC	31161619
EAN	8715494381475
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1.3/8 Inch
Length	300 mm
Class	Gr.B7M - Gr.2HM
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	8 Unified National
Threads per inch	8
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASTM	A193/A194
ASME	B16.5/B18.2.2
BS	≈4882

Technical Specification

B	2.1875
L (mm)	300

Technical Drawing

FABORY

