FABORY



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A320 - ASTM A194 Plain Gr.L7 - Gr.7 1.3/4X405 (16)

Article number	22326.444.406
Brand	-
UBB	500578311127
UNSPSC	31161619
EAN	8715494324434
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1.3/4 Inch
Length	405 mm
Class	Gr.L7 - Gr.7
Material	Steel
Material technical	ASTM A320 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	8 Unified National
Threads per inch	8
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASME	B16.5/B18.2.2
ASTM	A193/A194
BS	≈4882

Technical Specification

B	2.75
L (mm)	405

Technical Drawing

M	43.6

FABORY

