FABORY



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A320 - ASTM A194 Plain Gr.L7 - Gr.4 2 Inch X440 (17.1/4)

Article number	22330.508.438
Brand	-
UBB	500578964461
UNSPSC	31161619
EAN	8715494425872
PKG. of 1	Full Box Only

Technical Parameters

Diameter	2 Inch
Length	440 mm
Class	Gr.L7 - Gr.4
Material	Steel
Material technical	ASTM A320 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	8 Unified National
Threads per inch	8
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.Grade 4 nuts are no longer in ASTM A194/A194M and will be phased out gradually.

Standards

BS	≈4882
ASTM	A193/A194
ASME	B16.5/B18.2.2

It is advised to use Grade 7 nuts instead.

Technical Specification

B	3.125
L (mm)	440
M	50

Technical Drawing

