FABORY



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A320 - ASTM A194 Plain Gr.L7 - Gr.4 2.3/4X660 (26)

Article number	22330.698.660
Brand	-
UBB	500578972613
UNSPSC	31161619
EAN	8715494398558
PKG. of 1	Full Box Only

Technical Parameters

Diameter	2.3/4 Inch
Length	660 mm
Class	Gr.L7 - Gr.4
Material	Steel
Material technical	ASTM A320 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	8 Unified National
Threads per inch	8
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.Grade 4 nuts are no longer in ASTM A194/A194M and will be phased out gradually.

Standards

ASME	B16.5/B18.2.2
BS	≈4882
ASTM	A193/A194

It is advised to use Grade 7 nuts instead.

Technical Specification

B	4.25
L (mm)	660
M	68.7

Technical Drawing

