FABORY



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B16 - Gr.4 1 Inch X275 (10.3/4)

Article number	22554.254.273
Brand	-
UBB	500579062299
UNSPSC	31161619
EAN	8715494394239
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1 Inch
Length	275 mm
Class	Gr.B16 - Gr.4
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse
Threads per inch	8
Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.Grade 4 nuts are no longer in ASTM A194/A194M and will be phased

Standards

ASME	B16.5/B18.2.2
ASTM	A193/A194
BS	≈4882

out gradually. It is advised to use Grade 7 nuts instead.

Technical Specification

B	1.625
L (mm)	275
M	25

Technical Drawing

