FABORY



Slotted cheese head screw DIN 84 Steel Zinc plated yellow passivated 4.8 M2X12

Article number	24510.020.012
Brand	-
UBB	950353794528
UNSPSC	31161504
EAN	8715492628084
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M2
Length	12 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

DIN	84
ASME	≈B18.6.7M
NEN	≈1602
BS	≈4183
NF	≈E25-127
ISO	≈1207

Technical Specification

d-D	M2
Thread length (min.)	25
dk (max.)	3.8
Full thread if L ≤	30
k (max.)	1.3
L (mm)	12
n	0.5
P	0.4
t (min.)	0.5

Technical Drawing