FABORY



Slotted cheese head screw DIN 84 Steel Zinc plated yellow passivated 4.8 M2,5X10

Article number	24510.025.010
Brand	-
UBB	950353793041
UNSPSC	31161504
EAN	8715492628169
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M2.5
Length	10 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NEN	≈1602
ASME	≈B18.6.7M
ISO	≈1207
NF	≈E25-127
DIN	84
BS	≈4183

Technical Specification

d-D	M2.5
Thread length (min.)	25
dk (max.)	4.5
Full thread if L ≤	30
k (max.)	1.6
L (mm)	10
n	0.6
P	0.45
t (min.)	0.7

Technical Drawing