FABORY



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M2X20

Article number	24520.020.020
Brand	-
UBB	950353111749
UNSPSC	31161504
EAN	8715492629739
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M2
Length	20 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈1207
DIN	84
NEN	≈1602
BS	≈4183
ASME	≈B18.6.7M
NF	≈E25-127

Technical Specification

d-D	M2
Thread length (min.)	25
dk (max.)	3.8
Full thread if L ≤	30
k (max.)	1.3
L (mm)	20
n	0.5
P	0.4
t (min.)	0.5

Technical Drawing