FABORY



Slotted cheese head screw DIN 84 Steel Zinc plated 4.8 M6X12

Article number	24520.060.012
Brand	-
UBB	950353119197
UNSPSC	31161504
EAN	8715492630872
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	12 mm
Class	4.8
Driving features	Slotted
Head shape	Cylindrical head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
DIN	84
NEN	≈1602
ISO	≈1207
BS	≈4183
NF	≈E25-127

Technical Specification

d-D	M6
Thread length (min.)	38
dk (max.)	10
Full thread if L ≤	40
k (max.)	3.9
L (mm)	12
n	1.6
P	1
t (min.)	1.6

Technical Drawing