FABORY



Slotted countersunk head screw DIN 963 A Steel Zinc plated 4.8 M2,5X14

Article number	24540.025.014
Brand	-
UBB	950353878776
UNSPSC	31161504
EAN	8715492632654
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M2.5
Length	14 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
ASME	≈B18.6.7M
NF	≈E25-123
DIN	963
NEN	≈2370
ISO	≈2009

Technical Specification

d-D	M2.5
Thread length (min.)	18
dk (max.)	4.7
Full thread if L ≤	20
k (max.)	1.5
L (mm)	14
n	0.6
P	0.45
t (min.)	0.5

Technical Drawing

