FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M2,5X20

Article number	24540.025.020
Brand	-
UBB	950353130558
UNSPSC	31161504
EAN	8715492632685
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M2.5
Length	20 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈2009
NEN	≈2370
DIN	963
ASME	≈B18.6.7M
BS	≈4183
NF	≈E25-123

Technical Specification

d-D	M2.5
Thread length (min.)	18
dk (max.)	4.7
Full thread if L ≤	20
k (max.)	1.5
L (mm)	20
n	0.6
P	0.45
t (min.)	0.5

Technical Drawing

