FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M2,5X25

Article number	24540.025.025
Brand	-
UBB	950353130632
UNSPSC	31161504
EAN	8715492632692
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M2.5
Length	25 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
NF	≈E25-123
NEN	≈2370
ISO	≈2009
ASME	≈B18.6.7M
DIN	963

Technical Specification

d-D	M2.5
Thread length (min.)	18
dk (max.)	4.7
Full thread if L ≤	20
k (max.)	1.5
L (mm)	25
n	0.6
P	0.45
t (min.)	0.5

Technical Drawing

