FABORY



# Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M3X6

| | |
|---|---|
| Article number | 24540.030.006 |
| Brand | - |
| UBB | 950353131051 |
| UNSPSC | 31161504 |
| EAN | 8715492632838 |
| PKG. of 200 | Full Box Only |

## Technical Parameters

| | |
|---|---|
| Diameter | M3 |
| Length | 6 mm |
| Class | 4.8 |
| Driving features | Slotted |
| Head shape | Countersunk head |
| Material | Steel |
| Surface treatment | Zinc plated |
| Thread | Metric thread |

## Standards

| | |
|---|---|
| DIN | 963 |
| ISO | ≈2009 |
| BS | ≈4183 |
| ASME | ≈B18.6.7M |
| NF | ≈E25-123 |
| NEN | ≈2370 |

## Technical Specification

| | |
|---|---|
| d-D | M3 |
| Thread length (min.) | 19 |
| dk (max.) | 5.6 |
| Full thread if L ≤ | 22 |
| k (max.) | 1.65 |
| L (mm) | 6 |
| n | 0.8 |
| P | 0.5 |
| t (min.) | 0.6 |

## Technical Drawing

