FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M3,5X12

Article number	24540.035.012
Brand	-
UBB	950353132950
UNSPSC	31161504
EAN	8715492633088
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3.5
Length	12 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈2009
ASME	≈B18.6.7M
DIN	963
NF	≈E25-123
BS	≈4183
NEN	≈2370

Technical Specification

d-D	M3.5
Thread length (min.)	20
dk (max.)	6.5
Full thread if L ≤	25
k (max.)	1.93
L (mm)	12
n	0.8
P	0.6
t (min.)	0.7

Technical Drawing

