FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M3,5X25

Article number	24540.035.025
Brand	-
UBB	950353133297
UNSPSC	31161504
EAN	8715492633125
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3.5
Length	25 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
NF	≈E25-123
NEN	≈2370
BS	≈4183
DIN	963
ISO	≈2009

Technical Specification

d-D	M3.5
Thread length (min.)	20
dk (max.)	6.5
Full thread if L ≤	25
k (max.)	1.93
L (mm)	25
n	0.8
P	0.6
t (min.)	0.7

Technical Drawing

