FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M3,5X40

Article number	24540.035.040
Brand	-
UBB	950353133453
UNSPSC	31161504
EAN	8715492633156
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3.5
Length	40 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
DIN	963
ISO	≈2009
NEN	≈2370
BS	≈4183
NF	≈E25-123

Technical Specification

d-D	M3.5
Thread length (min.)	20
dk (max.)	6.5
Full thread if L ≤	25
k (max.)	1.93
L (mm)	40
n	0.8
P	0.6
t (min.)	0.7

Technical Drawing

