FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M5X35

Article number	24540.050.035
Brand	-
UBB	950353135920
UNSPSC	31161504
EAN	8715492633477
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	35 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	963
ASME	≈B18.6.7M
BS	≈4183
ISO	≈2009
NEN	≈2370
NF	≈E25-123

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if L ≤	30
k (max.)	2.5
L (mm)	35
n	1.2
P	0.8
t (min.)	1

Technical Drawing

