FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M6X35

Article number	24540.060.035
Brand	-
UBB	950353137413
UNSPSC	31161504
EAN	8715492633682
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	35 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈2009
BS	≈4183
NEN	≈2370
NF	≈E25-123
ASME	≈B18.6.7M
DIN	963

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if L ≤	35
k (max.)	3
L (mm)	35
n	1.6
P	1
t (min.)	1.2

Technical Drawing

