FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M12X25

Article number	24540.120.025
Brand	-
UBB	950353140870
UNSPSC	31161504
EAN	8715492634160
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	25 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	963
ISO	≈2009
BS	≈4183
ASME	≈B18.6.7M
NEN	≈2370
NF	≈E25-123

Technical Specification

d-D	M12
Thread length (min.)	46
dk (max.)	22
Full thread if L ≤	60
k (max.)	6
L (mm)	25
n	3
P	1.75
t (min.)	2.4

Technical Drawing

