FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M12X70

Article number	24540.120.070
Brand	-
UBB	950353141456
UNSPSC	31161504
EAN	8715492634238
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	70 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	963
NF	≈E25-123
BS	≈4183
ASME	≈B18.6.7M
NEN	≈2370
ISO	≈2009

Technical Specification

d-D	M12
Thread length (min.)	46
dk (max.)	22
Full thread if L ≤	60
k (max.)	6
L (mm)	70
n	3
P	1.75
t (min.)	2.4

Technical Drawing

