FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M16X30

Article number	24540.160.030
Brand	-
UBB	950353141787
UNSPSC	31161504
EAN	8715492634306
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M16
Length	30 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
NEN	≈2370
ASME	≈B18.6.7M
ISO	≈2009
NF	≈E25-123
DIN	963

Technical Specification

d-D	M16
Thread length (min.)	58
dk (max.)	29
Full thread if L ≤	70
k (max.)	8
L (mm)	30
n	5
P	2
t (min.)	3.2

Technical Drawing

