FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M20X70

Article number	24540.200.070
Brand	-
UBB	950353143015
UNSPSC	31161504
EAN	8715492634436
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M20
Length	70 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-123
BS	≈4183
ISO	≈2009
NEN	≈2370
ASME	≈B18.6.7M
DIN	963

Technical Specification

d-D	M20
Thread length (min.)	70
dk (max.)	36
Full thread if L ≤	80
k (max.)	10
L (mm)	70
n	5
P	2.5
t (min.)	4

Technical Drawing

