FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated yellow passivated 4.8 M4X12

Article number	24560.040.012
Brand	-
UBB	950353144591
UNSPSC	31161504
EAN	8715492634795
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	12 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

DIN	963
ISO	≈2009
NEN	≈2370
ASME	≈B18.6.7M
NF	≈E25-123
BS	≈4183

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if L ≤	25
k (max.)	2.2
L (mm)	12
n	1
P	0.7
t (min.)	0.8

Technical Drawing

