FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated yellow passivated 4.8 M5X16

Article number	24560.050.016
Brand	-
UBB	950353145333
UNSPSC	31161504
EAN	8715492634917
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	16 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NF	≈E25-123
NEN	≈2370
ASME	≈B18.6.7M
BS	≈4183
DIN	963
ISO	≈2009

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if L ≤	30
k (max.)	2.5
L (mm)	16
n	1.2
P	0.8
t (min.)	1

Technical Drawing

