FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated yellow passivated 4.8 M6X80

Article number	24560.060.080
Brand	-
UBB	951353498680
UNSPSC	31161504
EAN	8715492635112
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	80 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
ISO	≈2009
NEN	≈2370
DIN	963
BS	≈4183
NF	≈E25-123

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if L ≤	35
k (max.)	3
L (mm)	80
n	1.6
P	1
t (min.)	1.2

Technical Drawing

