FABORY



Slotted countersunk head screw DIN 963 Steel Zinc plated black passivated 4.8 M3X12

Article number	24565.030.012
Brand	-
UBB	950353621440
UNSPSC	31161504
EAN	8715492635280
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	12 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

Standards

NEN	≈2370
ASME	≈B18.6.7M
ISO	≈2009
NF	≈E25-123
BS	≈4183
DIN	963

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if L ≤	22
k (max.)	1.65
L (mm)	12
n	0.8
P	0.5
t (min.)	0.6

Technical Drawing

