FABORY



Cross recessed countersunk head screw DIN 965 A-H Steel Plain 4.8 M3X6

Article number	24569.030.006
Brand	-
UBB	500648243995
UNSPSC	31161504
EAN	8717077227033
PKG. of 2000	Full Box Only

Technical Parameters

Diameter	M3
Length	6 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Plain
Thread	Metric thread

Standards

NF	≈E25-119-1
ISO	≈7046-1
DIN	965

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if L ≤	22
k (max.)	1.65
L (mm)	6
No. cross recess	1
P	0.5

Technical Drawing

