FABORY



Cross recessed countersunk head screw DIN 965 A-H Steel Plain 4.8 M3X20

Article number	24569.030.020
Brand	-
UBB	500648244498
UNSPSC	31161504
EAN	8717077227088
PKG. of 2000	Full Box Only

Technical Parameters

Diameter	M3
Length	20 mm
Class	4.8
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	≈7046-1
DIN	965
NF	≈E25-119-1

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if L ≤	22
k (max.)	1.65
L (mm)	20
No. cross recess	1
P	0.5

Technical Drawing

