FABORY



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M3X40

Article number	24570.030.040
Brand	-
UBB	950353148147
UNSPSC	31161504
EAN	8715492635952
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	40 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-124
ASME	≈B18.6.7M
DIN	964
BS	≈4183
ISO	≈2010
NEN	≈2371

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
f ≈	0.75
Full thread if L ≤	22
k (max.)	1.65
L (mm)	40
n	0.8
P	0.5
t (min.)	1.2

Technical Drawing

