FABORY



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M4X25

Article number	24570.040.025
Brand	-
UBB	950353148899
UNSPSC	31161504
EAN	8715492636041
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	25 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
ISO	≈2010
BS	≈4183
DIN	964
NEN	≈2371
NF	≈E25-124

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
f ≈	1
Full thread if L ≤	25
k (max.)	2.2
L (mm)	25
n	1
P	0.7
t (min.)	1.6

Technical Drawing

