FABORY



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M4X50

Article number	24570.040.050
Brand	-
UBB	950353149137
UNSPSC	31161504
EAN	8715492636089
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	50 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	964
ISO	≈2010
NEN	≈2371
ASME	≈B18.6.7M
BS	≈4183
NF	≈E25-124

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
f ≈	1
Full thread if L ≤	25
k (max.)	2.2
L (mm)	50
n	1
P	0.7
t (min.)	1.6

Technical Drawing

