FABORY



Slotted raised countersunk head screw DIN 964 A Steel Zinc plated 4.8 M4X60

Article number	24570.040.060
Brand	-
UBB	950353149210
UNSPSC	31161504
EAN	8715492636096
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	60 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
NEN	≈2371
NF	≈E25-124
ISO	≈2010
DIN	964
BS	≈4183

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
f ≈	1
Full thread if L ≤	25
k (max.)	2.2
L (mm)	60
n	1
P	0.7
t (min.)	1.6

Technical Drawing

