FABORY



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M5X45

Article number	24570.050.045
Brand	-
UBB	950353150275
UNSPSC	31161504
EAN	8715492636218
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	45 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
NEN	≈2371
DIN	964
NF	≈E25-124
ASME	≈B18.6.7M
ISO	≈2010

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
f ≈	1.25
Full thread if L ≤	30
k (max.)	2.5
L (mm)	45
n	1.2
P	0.8
t (min.)	2

Technical Drawing

