FABORY



Slotted raised countersunk head screw DIN 964 Steel Zinc plated 4.8 M6X25

Article number	24570.060.025
Brand	-
UBB	950353150929
UNSPSC	31161504
EAN	8715492636294
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	25 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-124
ISO	≈2010
ASME	≈B18.6.7M
BS	≈4183
DIN	964
NEN	≈2371

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
f ≈	1.5
Full thread if L ≤	35
k (max.)	3
L (mm)	25
n	1.6
P	1
t (min.)	2.4

Technical Drawing

